

**Value pack DNMG indexable insert medium machining 30 pieces HB7020-2****Order data**

Order number	GG2438 160410L
GTIN	4067263094616
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	4 mm
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	130 - 370 mm/min
Feed f	0.2 - 0.5 mm/rev.
Main application	P
Number of changes/inserts	2
Contents	251038 HB7020-2
Tool material	Carbide
Cutting depth a_p	0.3 - 4 mm
Cutting depth $a_{p \min}$	0.65 mm
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2438 160410L

