

Garant
VCGT 160402, Grade: HU7310


Order data

Order number	261457 HU7310
GTIN	4045197671721
Item class	21G

Description

VCGT 160402 HU7310 Grade: HU7310
 Chip breaker: AM
 Tolerance: G
 Cutting depth a_p : 0.1 - 4 mm
 Feed f : 0.05 - 0.5 mm/rev.
 Cutting speed v_c main application: 350 - 600 m/min

Technical description

Cutting speed v_c main application	350 - 600 m/min
Cutting depth a_p	0.1 - 4 mm
Cutting conditions	continuous
Chip breaker	AM
Corner radius	0.2 mm
Main application	N
Feed f	0.05 - 0.5 mm/rev.

Grade	HU7310
Finishing/roughing assignment	Roughing
Finishing/roughing assignment	Finishing
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
Coating	uncoated
ISO code indexable insert	VCGT 160402
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning