

**Garant**
**VCGT 110301, Grade: HU7310**


### Order data

Order number	261452 HU7310
GTIN	4045197671523
Item class	21G

### Technical description

Feed f	0.05 - 0.5 mm/rev.
Main application	N
Cutting conditions	continuous
Chip breaker	AM
Cutting depth $a_p$	0.1 - 4 mm
Cutting speed $v_c$ main application	350 - 600 m/min
Corner radius	0.1 mm
Grade	HU7310
Finishing/roughing assignment	Roughing
Finishing/roughing assignment	Finishing
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning

Tool material	Carbide
Coating	uncoated
ISO code indexable insert	VCGT 110301
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning