

**CNMG indexable insert for finishing 50 pieces, HB7035-2, Size: 120408****Order data**

Order number	GG2406 120408
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.1 - 0.4 mm/rev.
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Main application	P
Cutting depth $a_{p \min}$	0.55 mm
Cutting speed v_c main application	150 - 350 mm/min
Contents	250060 HB7035-2
ISO code indexable insert	CNMG 120408
Number of changes/inserts	4
Cutting depth a_p	0.3 - 2 mm
Tool material	Carbide
Cutting depth $a_{p \max}$	4.25 mm
Quantity	50
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2406 120408
