

**Value pack CNMG indexable insert medium machining 30 pieces HB7010-2****Order data**

Order number	GG2407 120404
GTIN	4067263092278
Item class	GGN

Technical description

Main application	P
Number of changes/inserts	4
Tool material	Carbide
Cutting depth a_p	0.3 - 4 mm
Corner radius	0.4 mm
Cutting speed v_c main application	140 - 440 mm/min
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth $a_{p \max}$	4.25 mm
ISO code indexable insert	CNMG 120404
Contents	250156 HB7010-2
Feed f	0.2 - 0.5 mm/rev.
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2407 120404
