

Garant**CNMG indexable insert for finishing 30 pieces, HB7120-1, Size: 120404****Order data**

Order number	GG2900 120404
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Tool material	Carbide
Feed f	0.15 - 0.5 mm/rev.
Cutting depth $a_{p \min}$	0.25 mm
Main application	M
Contents	250058 HB7120-1
Corner radius	0.4 mm
Cutting speed v_c main application	90 - 290 mm/min
ISO code indexable insert	CNMG 120404
Cutting depth $a_{p \max}$	4.25 mm
Cutting depth a_p	0.3 - 2.5 mm
Number of changes/inserts	4
Quantity	30
Type	HB7120-1

Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2900 120404