

Garant**CCMT indexable insert for finishing 50 pieces, HB7035-2, Size: 060202****Order data**

Order number	GG2806 060202
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.15 mm
Number of changes/inserts	2
Corner radius	0.2 mm
Feed f	0.07 - 0.25 mm/rev.
ISO code indexable insert	CCMT 060202
Cutting depth $a_{p \max}$	2 mm
Cutting speed v_c main application	120 - 350 mm/min
Main application	P
Finishing/roughing assignment	Finishing
Contents	260050 HB7035-2
Tool material	Carbide
Cutting depth a_p	0.2 - 1.5 mm
Quantity	50

Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2806 060202