



Precision ER collet chuck CENTRO P, SK 50 A = 100, Type CP for ER: 32



Order data

Order number	300692 32
GTIN	4054631059872
Item class	33F

Description

Version:

- External and internal tapers ground. With Balluffchip- bore.
- Radial run-out and repetition accuracy 3µm at 3 × D, maximum 50 mm.
- Very high clamping forces due to the collet fully seated in the chuck and coated clamping nut.
- Vibration damping due to the element collet and mass of the chuck.
- Alternatively without seals with ER CP clamping nut No. 309655 or sealed system with ER clamping nut CP for HP sealing rings No. 309665 in conjunction with HP sealing rings No.309666 – 309668 (for internal coolant supply or as a dirt trap!).

Advantage:

Patented optimum seating of the collet, double guides, trapezoidal thread and low-friction coated clamping nut amalgamate when clamped into a sturdy unit, thus ensuring a very high degree of rigidity and precision.

Application:

For high precision clamping of tools with plain shank.

Supplied with:

Without clamping nut, without sealing rings.

Optional extras:

Pull-studs (PS) No. 308600 – 308806, PS pull stud wrenches No. 308820; 308835, precision ER collets for HP No. 309368 – 309378, and for taps No. 309402 – 309418 (not for Horex), ER CP clamping nuts No. 309655; 309665, HP sealing rings No. 309666 – 309668. CP roller bearing wrenches No. 309754; 309756.

Note:

- **CP chuck clamps only nominal Ø up to shank Ø tolerance h10.**
- **Use in combination with Fahrion collets.**

Machining strategy: HSC

Shape: ADB
Clamping range: 2 - 20 mm
External Ø D: 50 mm

Technical description

Clamping range	2 - 20 mm
Type CP for ER	32
External Ø D	50 mm
Shape	ADB
Series	Centro P
Adapter	SK 50 A = 100
Arbor standard	ISO 7388-1
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity ER collet with CP collet chuck	≤ 6 µm
Concentricity HP collet with CP collet chuck	≤ 3 µm
Machining strategy	HSC
Type of product	Collet chuck

Accessories

ER collet HP with seal Nominal clamping Ø d 19 mm	309377 19
CP roller bearing wrench for torque wrenches Type 32	309756 32
ER collet HP Nominal clamping Ø d 12 mm	309376 12
ER collet HP with seal Nominal clamping Ø d 16 mm	309377 16
ER collet for machine taps with seal Nominal clamping Ø d 6 mm	309414 6
ER collet HP with seal Nominal clamping Ø d 14 mm	309377 14
ER collet for machine taps with seal Nominal clamping Ø d 12 mm	309414 12
ER collet HP with seal Nominal clamping Ø d 12 mm	309377 12

ER collet HP Nominal clamping Ø d 5 mm	309376 5
ER collet for machine taps with seal Nominal clamping Ø d 14 mm	309414 14
ER collet HP with seal Nominal clamping Ø d 3 mm	309377 3
ER collet HP with seal Nominal clamping Ø d 5 mm	309377 5
Torque insert for Pull studs to SO 7388 suitable for ISO taper size 50	308812 50
ER collet HP Nominal clamping Ø d 4 mm	309376 4
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Pull stud 90° sealed suitable for steep tapers 50	308790 50
ER collet HP with seal Nominal clamping Ø d 17 mm	309377 17
ER collet HP with seal and spray nozzles Nominal clamping Ø d 20 mm	309378 20
Wrench for pull studs ISO 7388 suitable for ISO taper size 50	308830 50
ER collet HP Nominal clamping Ø d 16 mm	309376 16
ER collet HP with seal Nominal clamping Ø d 11 mm	309377 11
ER collet HP with seal Nominal clamping Ø d 20 mm	309377 20
ER collet HP with seal and spray nozzles Nominal clamping Ø d 16 mm	309378 16
ER collet HP Nominal clamping Ø d 20 mm	309376 20
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 18 mm	309418 18
Pull stud 45° sealed suitable for steep tapers 50	308765 50
ER collet HP with seal and spray nozzles Nominal clamping Ø d 4 mm	309378 4
ER collet HP with seal Nominal clamping Ø d 10 mm	309377 10
ER collet HP with seal and spray nozzles Nominal clamping Ø d 12 mm	309378 12
ER collet HP with seal and spray nozzles Nominal clamping Ø d 8 mm	309378 8
ER collet HP with seal Nominal clamping Ø d 4 mm	309377 4

ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 7 mm	309418 7
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 14 mm	309418 14
ER collet HP with seal and spray nozzles Nominal clamping Ø d 6 mm	309378 6
ER collet HP with seal Nominal clamping Ø d 9 mm	309377 9
ER collet HP with seal Nominal clamping Ø d 6 mm	309377 6
Pull stud Form A suitable for steep tapers 50	308600 50
Pull stud 60° sealed suitable for steep tapers 50	308785 50
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 20 mm	309418 20
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 6 mm	309418 6
ER collet for machine taps with seal Nominal clamping Ø d 11 mm	309414 11
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 4,5 mm	309418 4,5
ER collet HP with seal Nominal clamping Ø d 18 mm	309377 18
ER collet HP Nominal clamping Ø d 2 mm	309376 2
ER collet HP Nominal clamping Ø d 7 mm	309376 7
Pull stud stud sealed, form A suitable for steep tapers 50	308610 50
ER collet for machine taps with seal Nominal clamping Ø d 4,5 mm	309414 4,5
Torque insert for Pull studs to DIN 69872 suitable for ISO taper size 50	308810 50
ER collet HP with seal Nominal clamping Ø d 8 mm	309377 8
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 10 mm	309418 10
Pull stud 45° sealed suitable for steep tapers 50	308760 50
Pull stud Form B suitable for steep tapers 50	308640 50

ER collet for machine taps with seal Nominal clamping Ø d 9 mm	309414 9
ER collet HP with seal and spray nozzles Nominal clamping Ø d 10 mm	309378 10
ER collet HP Nominal clamping Ø d 11 mm	309376 11
ER collet HP Nominal clamping Ø d 9 mm	309376 9
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 12 mm	309418 12
Pull stud sealed, form B suitable for steep tapers 50	308650 50
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 11 mm	309418 11
ER collet HP Nominal clamping Ø d 17 mm	309376 17
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 50	308605 50
ER collet HP Nominal clamping Ø d 14 mm	309376 14
ER collet HP Nominal clamping Ø d 6 mm	309376 6
ER collet HP Nominal clamping Ø d 15 mm	309376 15
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 8 mm	309418 8
ER collet HP Nominal clamping Ø d 3 mm	309376 3
Special pull stud with no internal thread sealed suitable for steep tapers 50	308720 50
Pull stud sealed suitable for steep tapers 50	308660 50
ER collet HP Nominal clamping Ø d 8 mm	309376 8
Special pull stud with no internal thread sealed suitable for steep tapers 50	308700 50
ER collet HP Nominal clamping Ø d 19 mm	309376 19
CP roller bearing wrench Type 32	309754 32
ER collet for machine taps with seal Nominal clamping Ø d 8 mm	309414 8
Pull stud sealed, form B suitable for steep tapers 50	308620 50
Pull stud 90° sealed suitable for steep tapers 50	308795 50
ER collet HP Nominal clamping Ø d 13 mm	309376 13

ER collet HP Nominal clamping Ø d 18 mm	309376 18
ER collet HP with seal Nominal clamping Ø d 15 mm	309377 15
ER collet for machine taps with seal Nominal clamping Ø d 18 mm	309414 18
ER collet for machine taps with seal Nominal clamping Ø d 10 mm	309414 10
ER collet HP with seal and spray nozzles Nominal clamping Ø d 14 mm	309378 14
ER collet for machine taps with seal Nominal clamping Ø d 16 mm	309414 16
ER collet HP with seal Nominal clamping Ø d 7 mm	309377 7
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 9 mm	309418 9
ER collet HP with seal and spray nozzles Nominal clamping Ø d 18 mm	309378 18
ER collet for machine taps with seal Nominal clamping Ø d 7 mm	309414 7
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 50	308615 50
ER collet for machine taps with seal Nominal clamping Ø d 20 mm	309414 20
ER collet HP Nominal clamping Ø d 10 mm	309376 10
ER collet for machine taps with seal and spray nozzles Nominal clamping Ø d 16 mm	309418 16
ER collet HP with seal Nominal clamping Ø d 13 mm	309377 13