



CCMT indexable insert for medium machining 30 pieces, HB7010-2, Size: 060202



Order data

Order number	GG2807 060202
GTIN	4067263092278
Item class	GGN

Technical description

Corner radius	0.2 mm
Cutting depth $a_{p \max}$	2 mm
Feed f	0.08 - 0.3 mm/rev.
Cutting depth a_p	0.3 - 2 mm
Contents	260140 HB7010-2
Cutting depth $a_{p \min}$	0.15 mm
Finishing/roughing assignment	Finishing
Number of changes/inserts	2
Cutting speed v_c main application	120 - 440 mm/min
Main application	P
Tool material	Carbide
ISO code indexable insert	CCMT 060202
Quantity	30

Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2807 060202