

**Value pack CNMG indexable insert medium machining 30 pieces HB7010-2****Order data**

Order number	GG2407 160612
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.8 mm
ISO code indexable insert	CNMG 160612
Corner radius	1.2 mm
Cutting depth a_p	0.3 - 4 mm
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	5.5 mm
Tool material	Carbide
Feed f	0.2 - 0.5 mm/rev.
Contents	250170 HB7010-2
Cutting speed v_c main application	140 - 440 mm/min
Number of changes/inserts	4
Main application	P
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2407 160612
