


CCMT indexable insert for finishing 30 pieces, HB7130-2, Size: 120404

Order data

Order number	GG3501 120404
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	4.25 mm
Corner radius	0.4 mm
Main application	M
Tolerance	M
Cutting depth $a_{p \min}$	0.25 mm
Contents	260064 HB7130-2
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.2 - 2.5 mm
ISO code indexable insert	CCMT 120404
Cutting speed v_c main application	80 - 270 mm/min
Tool material	Carbide
Number of changes/inserts	2
Feed f	0.1 - 0.3 mm/rev.
Quantity	30

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3501 120404