

Garant**CCMT indexable insert for medium machining 30 pieces, HB7010-2, Size: 09T304****Order data**

Order number	GG2807 09T304
GTIN	4067263092278
Item class	GGN

Technical description

Tool material	Carbide
Main application	P
Cutting depth $a_{p \min}$	0.25 mm
Number of changes/inserts	2
Cutting depth a_p	0.3 - 2 mm
Feed f	0.08 - 0.3 mm/rev.
Cutting speed v_c main application	120 - 440 mm/min
Contents	260150 HB7010-2
ISO code indexable insert	CCMT 09T304
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	3.25 mm
Quantity	30

Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2807 09T304