

**Value pack CNMG indexable insert medium machining 30 pieces HB7035-2****Order data**

Order number	GG2409 120404
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	4.25 mm
Main application	P
Finishing/roughing assignment	Finishing
ISO code indexable insert	CNMG 120404
Cutting depth $a_{p \min}$	0.25 mm
Feed f	0.2 - 0.5 mm/rev.
Number of changes/inserts	4
Corner radius	0.4 mm
Cutting depth a_p	0.3 - 4 mm
Contents	250156 HB7035-2
Tool material	Carbide
Cutting speed v_c main application	120 - 320 mm/min
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2409 120404
