



SNMG indexable insert for medium machining 50 pieces, HB7020-2, Size: 120412

Order data

Order number	GG2450 120412
GTIN	4067263093121
Item class	GGN

Technical description

Contents	251226 HB7020-2
Number of changes/inserts	8
Finishing/roughing assignment	Finishing
Main application	P
ISO code indexable insert	SNMG 120412
Cutting depth $a_{p \max}$	4.25 mm
Corner radius	1.2 mm
Cutting depth $a_{p \min}$	0.8 mm
Cutting speed v_c main application	130 - 370 mm/min
Cutting depth a_p	0.3 - 4 mm
Feed f	0.2 - 0.5 mm/rev.
Tool material	Carbide
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2450 120412
