

**Value pack SNMG indexable insert roughing 50 pieces HB7020-2****Order data**

Order number	GG2453 150612
GTIN	4067263093305
Item class	GGN

Technical description

ISO code indexable insert	SNMG 150612
Contents	251330 HB7020-2
Cutting speed v_c main application	110 - 360 mm/min
Cutting depth $a_{p \max}$	5.25 mm
Main application	P
Cutting depth a_p	1.5 - 6 mm
Finishing/roughing assignment	Roughing
Tool material	Carbide
Feed f	0.25 - 0.6 mm/rev.
Number of changes/inserts	8
Cutting depth $a_{p \min}$	0.8 mm
Corner radius	1.2 mm
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2453 150612
