

**Value pack TNMG indexable insert finishing 30 pieces HB7020-2****Order data**

Order number	GG2455 160404
GTIN	4067263092278
Item class	GGN

Technical description

Tool material	Carbide
Cutting depth $a_{p \max}$	4 mm
Corner radius	0.4 mm
ISO code indexable insert	TNMG 160404
Cutting depth a_p	0.3 - 2 mm
Feed f	0.1 - 0.4 mm/rev.
Cutting depth $a_{p \min}$	0.25 mm
Main application	P
Cutting speed v_c main application	160 - 400 mm/min
Finishing/roughing assignment	Finishing
Contents	251432 HB7020-2
Number of changes/inserts	6
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2455 160404
