

Garant**CCMT indexable insert for finishing 50 pieces, HB7120-1, Size: 060202****Order data**

Order number	GG3503 060202
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	90 - 290 mm/min
Tolerance	M
Quantity	50
Number of changes/inserts	2
Feed f	0.1 - 0.3 mm/rev.
Contents	260050 HB7120-1
Cutting depth $a_{p \min}$	0.15 mm
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	2 mm
Main application	M
Corner radius	0.2 mm
Cutting depth a_p	0.2 - 2.5 mm
Tool material	Carbide

ISO code indexable insert	CCMT 060202
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3503 060202