

**TNMG indexable insert for finishing 50 pieces, HB7010-2, Size: 160404****Order data**

Order number	GG2457 160404
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.25 mm
Main application	P
ISO code indexable insert	TNMG 160404
Contents	251432 HB7010-2
Feed f	0.1 - 0.4 mm/rev.
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.3 - 2 mm
Number of changes/inserts	6
Tool material	Carbide
Cutting speed v_c main application	170 - 500 mm/min
Corner radius	0.4 mm
Cutting depth $a_{p \max}$	4 mm
Quantity	50
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2457 160404
