

Garant**CCMT indexable insert for finishing 50 pieces, HB7120-1, Size: 09T302****Order data**

Order number	GG3503 09T302
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	CCMT 09T302
Cutting depth $a_{p \min}$	0.15 mm
Cutting depth $a_{p \max}$	3.25 mm
Cutting speed v_c main application	90 - 290 mm/min
Feed f	0.1 - 0.3 mm/rev.
Tool material	Carbide
Main application	M
Tolerance	M
Corner radius	0.2 mm
Cutting depth a_p	0.2 - 2.5 mm
Quantity	50
Contents	260056 HB7120-1
Finishing/roughing assignment	Finishing

Data sheet

Number of changes/inserts	2
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3503 09T302