

Garant**VCMT indexable insert for finishing 50 pieces, HB7130-2, Size: 160404****Order data**

Order number	GG3568 160404
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.25 mm
Contents	261372 HB7130-2
Cutting speed v_c main application	80 - 270 mm/min
Tolerance	M
ISO code indexable insert	VCMT 160404
Tool material	Carbide
Cutting depth $a_{p \max}$	2.5 mm
Cutting depth a_p	0.2 - 1.5 mm
Feed f	0.1 - 0.3 mm/rev.
Main application	M
Number of changes/inserts	2
Quantity	50

Corner radius	0.4 mm
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3568 160404