

Garant**CCMT indexable insert for finishing 50 pieces, HB7120-1, Size: 120404****Order data**

Order number	GG3503 120404
GTIN	4067263092278
Item class	GGN

Technical description

Corner radius	0.4 mm
Quantity	50
Feed f	0.1 - 0.3 mm/rev.
Finishing/roughing assignment	Finishing
Main application	M
Cutting depth $a_{p \max}$	4.25 mm
Contents	260064 HB7120-1
ISO code indexable insert	CCMT 120404
Number of changes/inserts	2
Tool material	Carbide
Tolerance	M
Cutting depth a_p	0.2 - 2.5 mm
Cutting speed v_c main application	90 - 290 mm/min

Data sheet

Cutting depth $a_{p \min}$	0.25 mm
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3503 120404