

Garant**Eco lever lock toolholder, right-hand, Shank size / insert size L: 20/16mm****Order data**

Order number	271991 20/16
GTIN	4045197654441
Item class	21U

Description**Version:**

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and greater process reliability.

Supplied with:

With shim 1.5°.

Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No. 317900 – 319886.

Technical description

Clamping screw for shim	279824 1
Functional width L ₄	20 mm
Head length L ₁	30 mm
Shim 1.5°	272600 1.5
Shank size	20 mm
Clamping screw	279810 2
Overall length L	89 mm
Series	Eco
Insert size	16 mm

Application type	right-hand
Through-coolant	yes
Type of product	Boring bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/271991-20/16>