

**TNMG indexable insert for medium machining 50 pieces, HB7035-2, Size: 160404****Order data**

Order number	GG2465 160404
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Number of changes/inserts	6
Contents	251542 HB7035-2
Cutting depth $a_{p \min}$	0.25 mm
Feed f	0.2 - 0.5 mm/rev.
Cutting depth $a_{p \max}$	4 mm
Corner radius	0.1 mm
Tool material	Carbide
ISO code indexable insert	TNMG 160404
Cutting speed v_c main application	130 - 320 mm/min
Main application	P
Cutting depth a_p	0.3 - 4 mm
Quantity	50
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2465 160404
