

**TNMG indexable insert for medium machining 50 pieces, HB7035-2, Size: 160408****Order data**

Order number	GG2465 160408
GTIN	4067263092278
Item class	GGN

Technical description

Main application	P
Contents	251244 HB7035-2
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	130 - 320 mm/min
Cutting depth a_p	0.3 - 4 mm
ISO code indexable insert	TNMG 160408
Cutting depth $a_{p \min}$	0.55 mm
Number of changes/inserts	6
Feed f	0.2 - 0.5 mm/rev.
Tool material	Carbide
Cutting depth $a_{p \max}$	4 mm
Corner radius	0.1 mm
Quantity	50
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2465 160408
