

Garant
Combination face mill adapter Form ADB, SK 40 A = 160, Spigot Ø d1: 27mm

Order data

Order number	300895 27
GTIN	4045197285263
Item class	31A

Description
Version:

Taper shank, spigot, and all contact surfaces are ground at the collar. With Balluff/RFID chip bore.
GARANT –All shanks hard turned (for smooth cutting action!).

Application:

- **With drive key for mills with longitudinal keyway, e. g. DIN 841.**
- **With face mill drive ring for face mills with cross keyway, DIN 1880 and cutter heads to DIN 1830.**

Supplied with:

Drive key, face mill drive ring, and lock screw.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840.

Note:

Internal cooling available only with suitable tightening screw No. 309861.

Technical description

Spigot Ø d ₁	27 mm
Overhang dimension A	160 mm
Spare drive ring No. 309870	27
Suitable toggle spanner No. 309840	27
Milling mandrel length L ₃ with drive ring	21 mm

Milling mandrel length L_4	33 mm
External $\varnothing D$	48 mm
Spare milling cutter lock screw No. 309860 / 309861	27
Clamping $\varnothing D_1$	27 mm
Adapter	SK 40 A = 160
Standard	DIN 6358
Arbor standard	DIN 69871
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 5 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling cutter spigot

Accessories

Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Milling cutter lock screw for mandrel $\varnothing 40$ mm	309860 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Hurco 45° pull stud with 4-mm bore and fit sealed suitable for steep tapers 40	308801 40
Pull stud Mazak, form A suitable for steep tapers 40M	308670 40M
Toggle spanner for mandrel $\varnothing 40$ mm	309840 40
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Milling cutter lock screw for mandrel $\varnothing 27$ mm	309860 27
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40

Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Toggle spanner for mandrel Ø 27 mm	309840 27
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Face mill drive ring for mandrel Ø 27 mm	309870 27
Face mill drive ring for mandrel Ø 40 mm	309870 40