

Garant
MT reducing adapter with tang, Form AD, SK 40 short, MT internal: 1

Order data

| | |
|--------------|---------------|
| Order number | 301155 1 |
| GTIN | 4045197285874 |
| Item class | 31A |

Description
Version:

- **Ground internally and externally.**
- **With Balluff/RFID chip bore.**

GARANT –All shanks hard turned (for smooth cutting action!).

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Technical description

| | |
|---------------------------------------|---------------------|
| Overhang dimension A | 50 mm |
| Morse taper internal | 1 |
| External Ø D | 25 mm |
| Adapter | SK 40 short |
| Arbor standard | ISO 7388-1 |
| Shape | AD |
| Balance quality G at rotational speed | G 6.3 at 12,000 rpm |
| Concentricity | ≤ 8 µm |
| Type of product | Arbor adapter |

Accessories

| | |
|---|------------|
| Pull stud 90°sealed suitable for steep tapers 40 | 308795 40 |
| Pull studMori-Seiki, sealed, form A suitable for steep tapers 40 | 308625 40 |
| Pull studsealed, form A suitable for steep tapers 40 | 308610 40 |
| Pull studForm A suitable for steep tapers 40 | 308600 40 |
| Pull stud 45°sealed suitable for steep tapers 40 | 308760 40 |
| Pull studMazak, form A suitable for steep tapers 40M | 308670 40M |
| Pull studsealed, form B suitable for steep tapers 40 | 308650 40 |
| Special pull stud with internal thread suitable for steep tapers 40 | 308740 40 |
| Pull studMori-Seiki, sealed, form A suitable for steep tapers 40 | 308630 40 |
| Wrench for pull studsISO 7388 suitable for ISO taper size 40 | 308830 40 |
| Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40 | 308820 40 |
| Pull stud 90°sealed suitable for steep tapers 40 | 308790 40 |
| Pull studsealed suitable for steep tapers 40 | 308660 40 |
| Pull studForm B suitable for steep tapers 40 | 308640 40 |
| Pull stud, 18CrNiMo7Form A suitable for steep tapers 40 | 308605 40 |
| Pull stud Hurco 45° with fitsealed suitable for steep tapers 40 | 308802 40 |
| Pull stud 45°sealed suitable for steep tapers 40 | 308765 40 |
| Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40 | 308801 40 |
| Pull stud 60°sealed suitable for steep tapers 40 | 308785 40 |
| Pull studsealed, form B suitable for steep tapers 40 | 308620 40 |
| Pull studsealed suitable for steep tapers 40 | 308635 40 |
| Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40 | 308615 40 |

Special pull stud with no internal threadsealed suitable for steep tapers 40

308700 40

Pull stud Hurco 90° with fitsealed suitable for steep tapers 40

308806 40