



Value pack VNMG indexable insert finishing 30 pieces HB7020-2

Order data

Order number	GG2467 160408
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.1 - 0.4 mm/rev.
Cutting depth $a_{p \min}$	0.55 mm
Cutting speed v_c main application	160 - 400 mm/min
Corner radius	0.8 mm
Cutting depth $a_{p \max}$	2.5 mm
Cutting depth a_p	0.3 - 2 mm
Contents	251734 HB7020-2
Finishing/roughing assignment	Finishing
ISO code indexable insert	VNMG 160408
Tool material	Carbide
Main application	P
Number of changes/inserts	4
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2467 160408
