

**Value pack CNMG indexable insert roughing 30 pieces HB7035-2****Order data**

Order number	GG2415 160612
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.25 - 0.6 mm/rev.
Cutting depth a_p	1.5 - 6 mm
Cutting speed v_c main application	100 - 290 mm/min
ISO code indexable insert	CNMG 160612
Cutting depth $a_{p \min}$	0.8 mm
Main application	P
Finishing/roughing assignment	Roughing
Contents	250336 HB7035-2
Number of changes/inserts	4
Tool material	Carbide
Cutting depth $a_{p \max}$	5.5 mm
Corner radius	1.2 mm
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2415 160612
