

**Value pack VNMG indexable insert finishing 30 pieces HB7035-2****Order data**

Order number	GG2468 160408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	150 - 350 mm/min
Number of changes/inserts	4
Feed f	0.1 - 0.4 mm/rev.
Cutting depth $a_{p \min}$	0.55 mm
Cutting depth a_p	0.3 - 2 mm
Tool material	Carbide
Cutting depth $a_{p \max}$	2.5 mm
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Main application	P
ISO code indexable insert	VNMG 160408
Contents	251734 HB7035-2
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2468 160408
