

**VNMG indexable insert for finishing 50 pieces, HB7035-2, Size: 160404****Order data**

Order number	GG2471 160404
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	VNMG 160404
Main application	P
Finishing/roughing assignment	Finishing
Tool material	Carbide
Contents	251732 HB7035-2
Cutting depth $a_{p \max}$	2.5 mm
Cutting speed v_c main application	150 - 350 mm/min
Feed f	0.1 - 0.4 mm/rev.
Corner radius	0.4 mm
Cutting depth $a_{p \min}$	0.25 mm
Number of changes/inserts	4
Cutting depth a_p	0.3 - 2 mm
Quantity	50
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2471 160404
