

Garant**CNMG indexable insert for medium machining 50 pieces, HB7140-2, Size: 160612****Order data**

Order number	GG2911 160612
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	CNMG 160612
Finishing/roughing assignment	Finishing
Quantity	50
Number of changes/inserts	4
Cutting speed v_c main application	60 - 200 mm/min
Tolerance	M
Coating	coated
Cutting depth $a_{p \max}$	5.5 mm
Feed f	0.1 - 0.4 mm/rev.
Corner radius	1.2 mm
Main application	M
Tool material	Carbide
Cutting depth $a_{p \min}$	0.8 mm

Cutting depth a_p	0.5 - 4 mm
Contents	250170 HB7140-2
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2911 160612