

Garant
MT reducing adapter with tang, Form AD, SK 50 short, MT internal: 2

Order data

Order number	301170 2
GTIN	4045197285911
Item class	31A

Description
Version:

- **Ground internally and externally.**
- **With Balluff/RFID chip bore.**

GARANT –All shanks hard turned (for smooth cutting action!).

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Technical description

Morse taper internal	2
Overhang dimension A	60 mm
External Ø D	32 mm
Adapter	SK 50 short
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 12,000 rpm
Concentricity	≤ 8 µm
Type of product	Arbor adapter

Accessories

Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50
Pull studsealed, form B suitable for steep tapers 50	308620 50
Pull studsealed suitable for steep tapers 50	308660 50
Pull studsealed, form A suitable for steep tapers 50	308610 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Pull studForm A suitable for steep tapers 50	308600 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull studForm B suitable for steep tapers 50	308640 50
Pull studsealed, form B suitable for steep tapers 50	308650 50
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50