

**Heavy-duty power drill, Type: 720547****Order data**

Order number	075155 720547
GTIN	4014586874463
Item class	03F

Description**Version:**

Powerful power drill with speed control for flexible use in metal construction.

- **Reversible for thread tapping up to M12.**
- **High-quality SUPRA SK Röhm metal quick-release chuck.**
- **With torque slip clutch.**
- **1200 W high-power motor with stable torque.**

Advantage:

High-quality Röhm metal quick-release chuck.

Supplied with:

Quick-clamping drill chuck 3 – 16 mm, additional handle.

Note:

Suitable jobber drills can be found from No. 114000.

Technical description

maximum vibration to EN	< 2.5 m/s ²
Weight	3.5 kg
maximum twist drill size Ø in wood 1st speed	50 mm
Manufacturer's designation	BOS 16
Chuck clamping range	3 - 16 mm

Power consumption	1200 W
Drill chuck adapter	1/2 inch – 20 UNF
Maximum twist drill size Ø in steel 1st speed	16 mm
Speed range 1st speed	0 - 520 min ⁻¹
Power supply	Mains operated
Suitable for material	Steel
Type of product	Drill