

**Value pack VNMG indexable insert medium machining 30 pieces HB7010-2****Order data**

Order number	GG2472 160404
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Cutting speed v_c main application	140 - 440 mm/min
ISO code indexable insert	VNMG 160404
Cutting depth $a_{p \min}$	0.25 mm
Number of changes/inserts	4
Feed f	0.2 - 0.5 mm/rev.
Contents	251802 HB7010-2
Tool material	Carbide
Cutting depth a_p	0.3 - 4 mm
Cutting depth $a_{p \max}$	2.5 mm
Main application	P
Corner radius	0.4 mm
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2472 160404
