

**VNMG indexable insert for medium machining 50 pieces, HB7010-2, Size: 160404****Order data**

Order number	GG2475 160404
GTIN	4067263092278
Item class	GGN

Technical description

Main application	P
Cutting speed v_c main application	140 - 440 mm/min
Contents	251802 HB7010-2
Cutting depth $a_{p \max}$	2.5 mm
Finishing/roughing assignment	Finishing
Number of changes/inserts	4
Corner radius	0.4 mm
Tool material	Carbide
ISO code indexable insert	VNMG 160404
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth a_p	0.3 - 4 mm
Feed f	0.2 - 0.5 mm/rev.
Quantity	50
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2475 160404
