

**Value pack WNMG indexable insert finishing 30 pieces HB7010-2****Order data**

Order number	GG2478 060404
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Feed f	0.1 - 0.4 mm/rev.
Cutting depth a_p	0.3 - 2 mm
Main application	P
Number of changes/inserts	6
Corner radius	0.4 mm
Cutting depth $a_{p \max}$	2 mm
Tool material	Carbide
Cutting speed v_c main application	170 - 500 mm/min
Cutting depth $a_{p \min}$	0.25 mm
ISO code indexable insert	WNMG 060404
Contents	251952 HB7010-2
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2478 060404
