

**Value pack WNMG indexable insert finishing 30 pieces HB7010-2****Order data**

Order number	GG2478 060408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.55 mm
Contents	251954 HB7010-2
Cutting depth $a_{p \max}$	2 mm
Feed f	0.1 - 0.4 mm/rev.
Number of changes/inserts	6
Tool material	Carbide
Cutting depth a_p	0.3 - 2 mm
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
ISO code indexable insert	WNMG 060408
Main application	P
Cutting speed v_c main application	170 - 500 mm/min
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2478 060408
