



VCMT indexable insert for medium machining 30 pieces, HB7130-2, Size: 110304



Order data

Order number	GG3571 110304
GTIN	4067263097211
Item class	GGN

Technical description

Cutting depth a_p	0.5 - 2.5 mm
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth $a_{p \max}$	1.75 mm
Corner radius	0.4 mm
Tool material	Carbide
Feed f	0.1 - 0.4 mm/rev.
Finishing/roughing assignment	Finishing
Contents	261454 HB7130-2
ISO code indexable insert	VCMT 110304
Cutting speed v_c main application	70 - 240 mm/min
Main application	M
Tolerance	M
Number of changes/inserts	2
Quantity	30

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3571 110304