

Garant**Value pack WNMG indexable insert finishing 30 pieces HB7035-2****Order data**

Order number	GG2480 060404
GTIN	4067263092278
Item class	GGN

Technical description

Main application	P
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.25 mm
Cutting speed v_c main application	150 - 350 mm/min
Corner radius	0.4 mm
Cutting depth $a_{p \max}$	2 mm
Number of changes/inserts	6
Contents	251952 HB7035-2
Cutting depth a_p	0.3 - 2 mm
Feed f	0.1 - 0.4 mm/rev.
ISO code indexable insert	WNMG 060404
Tool material	Carbide
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2480 060404
