

**Value pack WNMG indexable insert finishing 30 pieces HB7035-2****Order data**

Order number	GG2480 060408
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.1 - 0.4 mm/rev.
Main application	P
Cutting depth $a_{p \min}$	0.55 mm
ISO code indexable insert	WNMG 060408
Cutting depth a_p	0.3 - 2 mm
Tool material	Carbide
Contents	251954 HB7035-2
Number of changes/inserts	6
Cutting speed v_c main application	150 - 350 mm/min
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	2 mm
Corner radius	0.8 mm
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2480 060408
