

Garant**VCMT indexable insert for medium machining 50 pieces, HB7120-1, Size: 110304****Order data**

Order number	GG3573 110304
GTIN	4067263092278
Item class	GGN

Technical description

Quantity	50
Tolerance	M
Cutting depth a_p	0.5 - 2.5 mm
ISO code indexable insert	VCMT 110304
Tool material	Carbide
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth $a_{p \max}$	1.75 mm
Cutting speed v_c main application	80 - 260 mm/min
Number of changes/inserts	2
Contents	261454 HB7120-1
Feed f	0.1 - 0.4 mm/rev.
Main application	M
Corner radius	0.4 mm

Data sheet

Finishing/roughing assignment	Finishing
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3573 110304