

**Value pack WNMG indexable insert medium machining 30 pieces HB7020-2****Order data**

Order number	GG2485 080404
GTIN	4067263093572
Item class	GGN

Technical description

Cutting speed v_c main application	130 - 370 mm/min
Corner radius	0.4 mm
Cutting depth a_p	0.3 - 4 mm
Tool material	Carbide
Contents	252068 HB7020-2
Cutting depth $a_{p \max}$	2 mm
Cutting depth $a_{p \min}$	0.25 mm
ISO code indexable insert	WNMG 080404
Number of changes/inserts	6
Feed f	0.2 - 0.5 mm/rev.
Main application	P
Finishing/roughing assignment	Finishing
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2485 080404
