


DCMW 11T308, KBN35M, Type: ME

Order data

Order number	265696 ME
GTIN	4960664544219
Item class	25H

Description
Version:

MEGACOAT coated CBN inserts. MultiEdge; 2 cutting edges per insert.

Technical description

Feed f	0.08 - 0.15 mm/rev.
Cutting conditions	continuous
Corner radius	0.8 mm
Cutting speed v_c main application	120 - 200 m/min
Cutting depth a_p	0.05 - 0.5 mm
Cutting edge version	ME
Grade	KBN35M
Finishing/roughing assignment	Finishing
Tool material	CBN

ISO code indexable insert	DCMW 11T308
Number of changes/inserts	2
Product name attribute	KBN35M
Type of product	Indexable insert for turning

User data

	Suitability	V _c	ISO code
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
irregular	suitable only under restricted conditions		
interrupted	suitable		
dry	suitable		