



CCMT indexable insert for medium machining 30 pieces, HB7130-2, Size: 09T304



Order data

Order number	GG3507 09T304
GTIN	4067263096153
Item class	GGN

Technical description

Cutting depth a_p	0.2 - 4 mm
Cutting speed v_c main application	70 - 240 mm/min
Main application	M
Feed f	0.1 - 0.4 mm/rev.
Contents	260150 HB7130-2
Number of changes/inserts	2
Tolerance	M
Tool material	Carbide
Cutting depth $a_{p \min}$	0.25 mm
Corner radius	0.4 mm
Cutting depth $a_{p \max}$	3.25 mm
Finishing/roughing assignment	Finishing
ISO code indexable insert	CCMT 09T304
Quantity	30

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3507 09T304