

Garant
Parting-off tool Steel, neutral, Blade height h₅ / groove width w: 19/3,1 mm

Order data

Order number	273551 19/3,1
GTIN	4045197698940
Item class	21W

Description
Suitable for :

Toolholder No. 273984 – 274000 or No. 319132; 319133 (VDI toolholder).

Supplied with:

Supplied with key No. 279850 1 for changing inserts.

axial grooving possible: no

for maximum workpiece Ø: 45 mm

Width b₂: 2.35 mm

Height h₁: 15.7 mm

Overall length L_{tot}: 86 mm

max. groove depth t_{max}: 20 mm

Technical description

Blade height h ₅	19 mm
Width b ₂	2.35 mm
Groove width w	3.1 mm
for maximum workpiece Ø	45 mm
Height h ₁	15.7 mm
Overall length L _{tot}	86 mm
max. groove depth t _{max}	20 mm
Application type	neutral
Through-coolant	no

axial grooving possible	no
Type of product	Parting-off tool