



CCMT indexable insert for medium machining 30 pieces, HB7130-2, Size: 09T308



Order data

Order number	GG3507 09T308
GTIN	4067263096177
Item class	GGN

Technical description

Cutting speed v_c main application	70 - 240 mm/min
Contents	260152 HB7130-2
Cutting depth $a_{p \min}$	0.55 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
Corner radius	0.8 mm
Cutting depth a_p	0.2 - 4 mm
Feed f	0.1 - 0.4 mm/rev.
Main application	M
Cutting depth $a_{p \max}$	3.25 mm
Number of changes/inserts	2
ISO code indexable insert	CCMT 09T308
Tolerance	M
Quantity	30

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3507 09T308