

**WNMG indexable insert for medium machining 50 pieces, HB7035-2, Size: 060404****Order data**

Order number	GG2489 060404
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	WNMG 060404
Tool material	Carbide
Cutting depth $a_{p \min}$	0.8 mm
Contents	252062 HB7035-2
Cutting depth $a_{p \max}$	2.75 mm
Corner radius	1.2 mm
Number of changes/inserts	6
Feed f	0.2 - 0.5 mm/rev.
Cutting speed v_c main application	120 - 320 mm/min
Main application	P
Cutting depth a_p	0.3 - 4 mm
Finishing/roughing assignment	Finishing
Quantity	50
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2489 060404
