


WNMG indexable insert for finishing 50 pieces, HBT130, Size: 060404

Order data

Order number	GG3983 060404
GTIN	4067263092278
Item class	GGN

Technical description

Contents	251938 HBT130
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth $a_{p \max}$	2 mm
Finishing/roughing assignment	Finishing
Main application	M
ISO code indexable insert	WNMG 060404
Feed f	0.15 - 0.45 mm/rev.
Cutting speed v_c main application	60 - 220 mm/min
Coating	TiCN
Cutting depth a_p	0.5 - 2 mm
Quantity	50
Number of changes/inserts	6
Tool material	Carbide
Corner radius	0.4 mm

Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MF
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3983 060404