


DNMG indexable insert for finishing 30 pieces, HB7120-1, Size: 150608

Order data

Order number	GG2918 150608
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	90 - 290 mm/min
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.3 - 2 mm
Cutting depth $a_{p \min}$	0.55 mm
Feed f	0.1 - 0.4 mm/rev.
Contents	250660 HB7120-1
ISO code indexable insert	DNMG 150608
Number of changes/inserts	4
Corner radius	0.8 mm
Cutting depth $a_{p \max}$	3.75 mm
Tool material	Carbide
Main application	M
Quantity	30
Type	HB7120-1

Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2918 150608