



CCMT indexable insert for medium machining 50 pieces, HB7140-2, Size: 060202



Order data

Order number	GG3512 060202
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Tool material	Carbide
Number of changes/inserts	2
Cutting speed v_c main application	60 - 200 mm/min
Cutting depth a_p	0.2 - 4 mm
Cutting depth $a_{p \max}$	2 mm
Quantity	50
Feed f	0.1 - 0.4 mm/rev.
Cutting depth $a_{p \min}$	0.15 mm
Contents	260140 HB7140-2
Main application	M
Corner radius	0.2 mm

Data sheet

Coating	coated
Tolerance	M
ISO code indexable insert	CCMT 060202
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3512 060202